



Part Number : [194390005](#)

Product Description : Loxon Locking Quick Disconnect, Female, for 10-12 Wire, Reel, Tab 6.35 x 0.81mm

Series Number : 19439

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : CZ-4152

Documents and Resources

Drawings

[194390005_sd.pdf](#)

[194390009-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19439
Description	Loxon Locking Quick Disconnect, Female, for 10-12 Wire, Reel, Tab 6.35 x 0.81mm
Product Name	Loxon
Style	Locking Terminal
Type	Loxon Locking Disconnect
UPC	193264611676

Agency

UL	E79133
----	--------

Electrical

Voltage - Maximum	600V AC
-------------------	---------

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.950/g

Orientation	Straight
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-40° to +149°C
Wire Insulation Diameter	4.05-4.90mm
Wire Size (AWG)	10, 12

Mates With / Use With

Use with Part(s)

Description	Part Number
Loxon Locking Quick Disconnect Housing, Nylon, UL94V-2, Natural	<u>194390007</u>
Loxon Locking Quick Disconnect Housing, Nylon, UL94V-0, Natural	<u>194390008</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Locking Quick Disconnect Crimp Terminals, 12-10 AWG	<u>2133094300</u>
FineAdjust Applicator for Loxon Terminals, 12-10 AWG, UL 1015 Wire	<u>2037029400</u>

This document was generated on Apr 29, 2026