




Specifications:
Material: Copper Tube, Tin Plated
Operating Temperature Range: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$

Part No	Color	Dim.F ±0.40	Dim.L ±1.50	Dim.C +0.14 -0.00	Dim.W ±0.20	Wire Range AWG mm ²
3060-06100G	YELLOW	6.0	12.0	1.40	3.00	17AWG 1.0mm ²
3060-06100D	RED					
3060-08100G	YELLOW	8.0	14.0			
3060-08100D	RED					
3060-10100G	YELLOW	10.0	16.0			
3060-10100D	RED					
3060-12100G	YELLOW	12.0	18.0			
3060-12100D	RED					
Part No	Color	Dim.F ±0.40	Dim.L ±1.50	Dim.C +0.25 -0.00	Dim.W ±0.20	Wire Range AWG mm ²
3060-08150G	RED	8.0	14.0	1.70	3.50	16AWG 1.5mm ²
3060-08150D	BLACK					
3060-10150G	RED	10.0	16.0			
3060-10150D	BLACK					
3060-12150G	RED	12.0	18.0			
3060-12150D	BLACK					
Part No	Color	Dim.F ±0.40	Dim.L ±1.50	Dim.C +0.25 -0.00	Dim.W ±0.20	Wire Range AWG mm ²
3060-08250F	GRAY	8.0	14.0	2.20	4.20	14AWG 2.5mm ²
3060-08250D	BLUE					
3060-12250D	BLUE	12.0	18.0			
3060-18250D	BLUE	18.0	24.0 ±2.0			

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE:	CnC Tech Industrial Cable and Connector Technology	
				SELIN	.X ± 0.20 .XX ± 0.15		
				CHECKED:	UNIT: MM	DESCRIPTION:	SIZE
				JERRY	SCALE: 1:1		
A	09-JAN-2023			APPROVAL:	SHEET: 1 / 1	PART NO:	A4
REV	DATE	FILE	BY	RORY	PROJECTION:		
						3060-XXXXXX	