

Power It! 6-Outlet Power Strip, 15 ft. (4.57 m) Cord

MODEL NUMBER: **PS615**



Highlights

- 6 outlets
- Illuminated on/off switch
- 15-amp circuit breaker
- 15-ft. (4.57 m) power cord
- Keyhole mounting slots

Package Includes

- PS615 power strip
- Warranty information
- Instruction manual

Description

The Power It!® PS615 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes six NEMA 5-15R outlets, 15-foot (4.6-meter) AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

Features

- 6 outlets
- 15-ft. (4.57 m) cord
- 15 amp resettable circuit breaker
- Can accommodate 1 large transformer plug without covering remaining outlets, 3 total transformers
- Keyhole support for wall mounting
- Lighted power switch
- 120V AC, 50/60Hz electrical compatibility
- UL certification

Specifications

OVERVIEW	
UPC Code	037332175557
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT



Powering Business Worldwide

TRIPP LITE
SERIES

Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
PHYSICAL	
Color	Light Gray
Material of Construction	Plastic
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 101mm, distance between slot height = 28mm
Outlets Measurement (Center to Center)	1.12 in.
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	13.10 x 2.00 x 6.00
Shipping Dimensions (hwd / cm)	33.27 x 5.08 x 15.24
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
Unit Dimensions (hwd / in.)	10.800 x 1.850 x 1.230
Unit Dimensions (hwd / cm)	27.43 x 4.70 x 3.12
Unit Weight (lbs.)	1.6



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (kg)	0.73
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.