



Part Number : [936000041](#)
Product Description : Heavy-Duty Metal Cable Gland, with Washer and Gaskets, Pg16 Thread
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Number : 7000.6843.0



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Cable Gland, with Washer and Gaskets, Pg16 Thread
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 7.50, 10.00, 12.50, and 15.00mm internal diameters.
IP Rating	IP66
Product Name	Heavy-Duty Connectors
UPC	887191826134

Physical

Cable Diameter	7.00-14.50mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	21.000/g
Packaging Type	Bag
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg16
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Enclosures Size A and B metal type

This document was generated on Sep 24, 2025