

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RW8244-P4**BZ-2RW8244-P4****M**DRAWING
NUMBER

8

ISSUE

REPLACES

RELEASE NO. PR-1926

CHECK

CHECK

71 JUN 71


DAW

71 JUN 71

OMW

21 JUN

FORMTEK

**NOTES**

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $.139$ MAX DIA ON $1.000 \pm .002$ CENTERS
- 2 - SWITCH WILL WITHSTAND TEMPERATURE OF $400^{\circ} F$ FOR 100 HOURS
- 3 - 3X BINDING HEAD TERMINAL SCREW AND 3X CUPWASHER FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE-----2 1/2 OZ MAX

RELEASE FORCE-----1/2 OZ MIN

DIFFERENTIAL TRAVEL-----.007-.050

OVERTRAVEL-----.219 MIN

ELECTRICAL DATA**CONTACT ARRANGEMENT**
S P D T

UNDERWRITERS' LAB. INC. LISTED RATING

-L35- 5A-125, 250 OR 480 VAC

1/2A-125 VDC; 1/4A-250 VDC

-L288-

**SCALE FULL**

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES

WEIGHT .073 LB