



# C5, Bronze Ground Clamp, Cable to Water Pipe

By Burndy  
Catalog # C5

Bronze Ground Clamp, 10-2 AWG, 1/2"-1" Water Pipe.

## Features

- Connects grounding conductor to water pipe or copper tube
- Supplied with Zinc-plated steel hardware

## Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube

## General

Catalog Number	C5
EU RoHS Indicator	Yes
Material	Bronze Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Sub Brand	C DIE
Type	Junior
UPC	781810142295
UPC 14 Digit GTIN	00781810142295

## Dimensions

Dimension - Height inch	1.56 in
Dimension - Height mm	39.6 mm
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - Pad Width inch	0.50 in
Dimension - Width inch	0.56 in
Dimension - Width mm	14 mm

## Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG

Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1

## Product Assets

- 3D Models - C5\_MODEL-IGES
- 3D Models - C5\_MODEL-STEP
- 3D Models - C5\_MODEL-PDF
- Catalogs - Burndy Grounding Catalog
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Customer Notices - Prop 65 Notice
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR\_CN\_LineArt
- Sales Drawings - sc210654-01
- Specifications - C5

