


Slim High-Speed HDMI Cable with Ethernet and Digital Video with Audio, UHD 4K (M/M), 6 ft. (1.83 m)

MODEL NUMBER: **P569-006-SLIM**



Transmits digital audio/video and Ethernet signals from an HDMI source to a 4K-enabled television, projector or monitor. Recommended for home theater systems and digital signage. Slim design increases airflow in tight spaces.

Features

Connects HDMI Source to 4K TV, Projector or Monitor

- Ideal for home theater systems, digital signage and other applications that display UHD video and multi-channel audio

High Performance and Wide Compatibility

- Supports UHD video resolutions up to 4K, and 3D
- Audio return channel simplifies setup between display and receiver
- Supports iPad2 video mirroring when used with Apple digital A/V adapter
- Backward compatible with previous HDMI generations
- Works in all HDMI cabling scenarios

Special Slim Design

- Improved airflow in tight spaces
- Better flexibility for installing around corners and through cable management panels

Superior Construction Ensures a Flawless Signal

- Fully molded 36 AWG construction with integral strain relief for durability and long life
- Premium foil and braid shielding for EMI/RFI noise protection
- Corrosion-resistant gold-plated connectors and contacts for optimal signal transfer
- Flexible PVC jacket easy to install in tight spaces

Highlights

- Supports UHD video resolutions up to 4K
- Easy to install around corners and through management panels
- Premium foil and braid shielding protects against EMI/RFI noise
- Gold-plated connectors and contacts for optimal signal transfer

Package Includes

- P569-006-SLIM Slim High-Speed HDMI Cable with Ethernet and Digital Video with Audio (M/M), 6 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332199362
Product Type	Passive
Technology	HDMI
VIDEO	
Max Supported Video Resolution	3840 x 2160 @ 30Hz
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
EDID Support	Yes
Signal Transmission	Bidirectional
AUDIO	
Audio Specification	Stereo Audio
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	0
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.6mm
Wire Gauge (AWG)	34
Cable Length (ft.)	3
Cable Length (m)	0.91
Ferrite Core	No
Minimum Bend Radius	36mm
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.04



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	0.08
ENVIRONMENTAL	
Operating Temperature Range	32 TO 113 F (0 TO 45 C)
Storage Temperature Range	-40 - 80 °C (-40 - 176 °F)
Operating Humidity Range	10 to 85% RH, Non-Condensing
Storage Humidity Range	5 to 90% RH, Non-Condensing
COMMUNICATIONS	
Consumer Electronics Control (CEC) Supported	Yes
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Latching Connector	No
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Gripping Connector	No
FEATURES & SPECIFICATIONS	
HDCP Specification	1.4
EMI/RFI Line Noise Protection	No
MST Support	No
IP68 Rated	No
Antibacterial	No
Armored Cable	No
Ethernet Support	Yes
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>