



✓ Active

TE CONNECTIVITY (TE)

44A1131-22-3/6/9-9

Raychem | RC , SP

44A1131-22-3/6/9-9

TE Internal Number: 382523-000

Alias ID: 7-1192864-6

EU RoHS Compliant

EU ELV Compliant

Cable Type Spec 44

Conductor Diameter .79 mm [.031 in]

Number of Strands 19

Strand Size (AWG) 34

Overall Outside Diameter 3.56 mm [.14 in]

PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

THREE CONDUCTOR CABLE, RADIATION-CROSSLINKED, POLYALKENE-INSULATED, SHIELDED, JACKETED, LIGHTWEIGHT, GENERAL PURPOSE, 600 VOLT

PDF

English

CABLE, RADIATION-CROSSLINKED, POLYALKENE-INSULATED, THREE CONDUCTOR, SHIELDED, JACKETED, LIGHTWEIGHT, GENERAL PURPOSE

PDF [\(TIFF AVAILABLE\)](#)

English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Polyalkene-Insulated, Copper Or Copper Alloy

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 44

Shielded Yes

Cable Style Jacketed, Round Braided

Product Type Cable

Product Classification Cable - High Performance - Spec 44, 55 & RCW

Configuration Features

Number of Strands 19

Number of Conductors 3

Conductor Configuration Twisted Triple

Electrical Characteristics

Voltage Rating (V) 600

Body Features

Shield Material Tin-Coated Copper

Jacket Color White

Wire Color Blue, Orange, White

Conductor Material Tin-Plated Copper

Shield Diameter 3.15 mm [.124 in]

Dimensions

Conductor Diameter .79 mm [.031 in]

Strand Size (AWG) 34

Overall Outside Diameter 3.56 mm [.14 in]

Wire Size (AWG) 22

Usage Conditions

Operating Temperature Range (°C) -65 – 150

PRODUCT COMPLIANCE**Statement of Compliance****Statement of Compliance**

PDF

