



**Part Number :** [1300150091](#)

**Product Description :** Mini-Change C-Size Receptacle, 12 Poles, 1/2" - 14 NPT Threads, Male (Straight) to 16 AWG Leads, 5.0m (16.40') Length

**Series Number :** 130015

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** 3R2006A20M050



---

## Documents and Resources

### Drawings

[1300150091\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	130015
Description	Mini-Change C-Size Receptacle, 12 Poles, 1/2" - 14 NPT Threads, Male (Straight) to 16 AWG Leads, 5.0m (16.40') Length
Comments	C-Size (1-1/8" - 16 UN-2A)
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	78678884581

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	600V AC/DC

### Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	5.0m
Material - Component	Zinc Die-Cast with Black Epoxy

Mounting Thread Size	1/2" - 14 NPT
Net Weight	666.000/g
Orientation	Straight
Panel Mount	Front
Poles	12
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1015
Wire Size (AWG)	16

---

This document was generated on Jan 01, 2026