

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 10768569

☐ Compare

211PC069S0049 - 6 Way Female sealed SICMA Connector black Generation 1

☐ Compare

6 Way Female sealed SICMA Connector black Generation 1

Part # 211PC069S0049

[Question about this product?](#)



Attributes

Documents (1)

Related Products (22)

Part # :	211PC069S0049
Description :	6 Way Female sealed SICMA Connector black Generation 1
Product Type :	Connector
Status :	✓ Active
Family :	Mixed
Series :	Sicma 1.5 / 2.8
Cavities :	6
Terminal(s) blade size [mm] :	1.5, 2.8
Sealable :	Sealed
Gender :	Female
Material :	PBT
Weight [g] :	12
Connector Color :	Black
Remarks :	Former FCI Product, Delphi PN:10768569, Reduced size sealed housing - Sealing protection IP 75, Female part can be used as an aggregate housing, Circumferential interface seal, Rear sealing ensured by a pre-mounted mat-seal, Pre-assembled front grids support blade terminal guiding and mating, Terminal position assurance (T.P.A.) and connection position assurance (C.P.A.) option available, Acceptable wire size range from 0.5 to 2 mm ² for 1.5 mm and 0.5 to 4 mm ² for 2.8 mm
Application :	Inline (Wire to Wire), Switch - Door

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.