

AIMB-581

**Intel® Xeon® E3/ Core™ i7/i5/i3
LGA1155 MicroATX with CRT/DVI/LVDS,
6 COM, Dual LAN, DDR3 and SATAIII**

NEW



Features

- Supports Intel® Xeon®/Core™ i7/i5/i3 processor with Q67/C206 chipset
- Four DIMM sockets support up to 16 GB DDR3 1066/1333 MHz SDRAM
- Supports dual display of CRT, DVI, LVDS (optional) and dual GbE LAN
- Supports Intel vPro, AMT 7.0, PECI 3.0, USB 3.0, Software RAID 0, 1, 5, 10, TPM 1.2 (optional)
- Supports SUSIAccess and Embedded Software APIs

Software APIs:




Utilities:



Specifications

Processor System	CPU	Intel Xeon E3-1275	Intel Xeon E3-1225	Intel Core i3-2120	Intel Pentium G850	Intel Core i7-2600	Intel Core i5-2400	Intel Core i3-2120	Intel Celeron G540
	Core Number	4	4	2	2	4	4	2	2
	Max. Speed	3.4 GHz	3.1 GHz	3.3 GHz	2.9 GHz	3.4 GHz	3.1 GHz	3.3 GHz	2.5 GHz
	Integrated Graphic	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	L3 Cache	8 MB	6 MB	3 MB	3 MB	8 MB	6 MB	3 MB	2 MB
	Supports Model	WG2	WG2	WG2	WG2/QG2	QG2	QG2	QG2	QG2
	Chipset	Q67/C206							
Expansion Slot	BIOS	AMI EFI 64 Mbit SPI							
	PCI	32-bit/33 MHz, 2 slots							
	PCIe x4 (Gen2)	2.0 GB/s per direction, 1 slot							
	PCIe x16 (Gen2)	8 GB/s per direction, 1 slot							
Memory	Technology	Dual Channel DDR3 1066/1333 MHz SDRAM							
	Max. Capacity	16 GB							
	Socket	4 x 240-pin DIMM							
Graphics	Controller	Intel HD Graphics							
	VRAM	1 GB maximum shared memory with 2 GB and above system memory installed							
	LVDS	Single channel 24-bit/dual channel 48-bit LVDS (Optional for AIMB-581QG2-LVA1E sku)							
	1st DVI	Yes, supports max. resolution 1920 x 1200							
	2nd DVI	Yes, with internal pin header, supports max. resolution 1920 x 1200 (Optional. No populated on MP version)							
	Dual Display	CRT+LVDS, CRT+DVI, LVDS+DVI							
Ethernet	Interface	10/100/1000 Mbps							
	Controller	GbE LAN1: Intel 82579LM, GbE LAN2: Intel 82583V							
	Connector	RJ-45 x 2							
SATA	Max Data Transfer Rate	600 MB/s (SATA 3.0)/ 300 MB/s (SATA 2.0)							
	Channel	2/4							
Rear I/O	CRT	1							
	DVI	1							
	Ethernet	2							
	USB	4 (2 USB 2.0, 2 USB 3.0)							
	Audio	2 (Mic-in, Line-out)							
	Serial	2 (RS-232)							
	PS/2	2 (1 x keyboard and 1 x mouse)							
Internal Connector	USB	8 (USB 2.0 compliant)							
	Serial	4 (3 x RS-232, 1 x RS-232/422/485 to support auto flow control)							
	IDE	-							
	SATA	2 x 600 MB/s (SATA 3.0)/4 x 300 MB/s (SATA 2.0)							
	LVDS & Inverter	1 (Optional for AIMB-581QG2-LVA1E sku)							
	Parallel	1							
	IrDA	-							
	GPIO	8-bit GPIO							
Watchdog Timer	Output	System reset							
	Interval	Programmable 1 ~ 255 sec/min							
Power Requirements	Power On	Intel Core i7-2600 3.4GHz, 2GB DDR3 1333 MHz x 4pcs							
		5V	3.3V	12V	5Vsb	-12V			
		3.52 A	1.07 A	3.79 A	0.32 A	0 A			
Environment		Operating					Non-Operating		
	Temperature	0 ~ 60° C (32 ~ 140° F), depends on CPU speed and cooler solution					-20 ~ 70° C (-4 ~ 158° F)		
	Humidity	10-95% @ 40° C, non-condensing					10-95% @ 40° C, non-condensing		
	Note: The spec above is based on board test only.								
Physical Characteristics	Dimensions	244 mm x 244 mm (9.6" x 9.6")							

Block Diagram



Ordering Information

Part Number	Chipset	Memory	USB 3.0	CRT	DVI 1/2	LVDS	USB	COM	TPM	GbE LAN
AIMB-581QG2-00A1E	Q67	Non-ECC	2	Yes	1/(1)	(1)	12	6	(1)	2
AIMB-581WG2-00A1E	C206	ECC/Non-ECC	2	Yes	1/(1)	(1)	12	6	(1)	2
AIMB-581QG2-LVA1E	Q67	Non-ECC	2	Yes	1/(1)	1	12	6	(1)	2

*() not populated on MP version.

Riser Card

Part Number	Description
AIMB-RP10P-01A1E	1U riser card with 1 PCIe expansion
AIMB-RP30P-03A1E	2U riser card with 3 PCIe expansion
AIMB-RP3PF-21A1E	2U riser card for 1 PCIe x 16 abd 2 PCIe expansion
AIMB-RP3P8-12A1E	2U riser card with 2 PCIe x 8 & 1 PCI slots expansion (For WG2 Sku)

Note: AIMB-RP3P8-12A1E is not compatible with ACP-2010MB/2320MB chassis unless change special bracket to 1950014302N001.

I/O View



AIMB-581QG2-00A1E
AIMB-581WG2-00A1E
AIMB-581QG2-LVA1E

Packing List

Part Number	Description	Quantity
1700003194	SATA HDD cable	2
1703150102	SATA power cable	2
1960050472T000	I/O port bracket	1
2002058100	Startup manual	1
2062058100	Driver CD	1

Optional Accessories

Part Number	Description
1700002204	Dual port USB cable (27 cm) with bracket
1960047669N001	LGA1156 CPU cooler for 4U and wallmount chassis
1960047831N001	LGA1156 CPU cooler for 2U and wallmount chassis
1960049408N001	LGA1156 CPU cooler for 1U and wallmount chassis
1700008809	Printer port cable kit
1700018699	KBMS cable 1*6P-2.5/DIN-6P(F)*2, 25 cm
1700000447	1-to-4 serial ports cable kit, 45cm
1701400181	1-to-4 serial ports cable kit, 18cm
1700008822	DVI cable
1960055954T000	1U I/O port bracket
1950014302N001	Special bracket for riser card AIMB-RP3P8-12A1E

Note: Purchasing AIMB-581's proprietary CPU cooler from Advantech is a must, other brand's CPU cooler are NOT compatible with AIMB-581.

Embedded OS/API

OS/API	Part No.	Description
Win XPE	2070010800	XPE WES 2009 V4.0 ENG with Acronis PSNL
	2070010820	XPE WES09 AIMB-581 V4.0 ENG_CHT ATI PSNL
	2070011360	WES09 AIMB-581QG2 V4.1 ENG_JPN ATIP
	2070011525	WES7E AIMB-581 V5.1.3 ENG/CHT/CHS/JPN SA
	2070011526	Image WES7E AIMB-581 V5.6.3 ENG/CHT/CHS/JPN SA
Software API		SUSI 3.0 SW API for AIMB-581 XP