

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=10134371-001LF* > 10134371-001LF

10134371-001LF

10134371-001LF : Disconnecting knife SCREW Terminal Block F4

ACTIVE

RoHS Compliant

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Customer drawing

Environmental Compliance Report

Specifications

Download document

General	
Pollution Degree	3
Insulating Material Group	I
Number of contacts (Total)	2
Number of decks	Single
Packaging	Pack
Product Type	Universal Terminal Blocks
Attachment type (Board)	DIN Rail
Dimensional	
Width	5 mm
Conductor cross section solid (min-max)	0,5 / 4 sqmm
Conductor cross section stranded (min-max)	0,5 / 4 sqmm
Length (Overall)	58,9 mm
Strip length (Wire)	max 9 mm
Solid wire size (AWG)	24-10
Height (Total)	29,5 mm
Electrical	
Nominal Current	25 A
Nominal Voltage	300 V
Rated Surge Voltage	8kV
Surge Voltage Category	III
Current Rating (Max)	25 A
Physical	
Color (Housing)	Grey
Installation Torque	0,45 Nm
Flammability rating	UL 94 V-2
Material (Insulator)	PA
Approvals / Certifications	
Approvals / Certifications	cURus
Mounting	
Mounting style	Omega TH 35

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.