


RED INDICATES ORIGINAL

DATA CONTAINED IN THIS DOCUMENT IS
PROPRIETARY TO TROMPETER ELECTRONICS INC.
AND SHALL NOT BE DISCLOSED, COPIED OR USED
FOR PROCUREMENT OR MANUFACTURE WITHOUT
EXPRESS WRITTEN PERMISSION.


DASH NO	MODEL NO	IMPD OHMS
-1	BJ21	50
-2	UBJ21	75

INCH	MM
.005	0.13
.030	0.76
.060	1.52
.147	3.73
.218	5.54
.221	5.61
.380	9.65
.505	12.83
.510	12.95
.562	14.27
.757	19.23
1.050	26.92



-1 SHOWN

4. 50 & 75 OHM COAXIAL REAR MOUNT
INSULATED 2-LUG BNC TYPE
SOLDER POT BULKHEAD
RECEPTACLE
3. MAX PANEL THK: .147
2. FINISH: TFS-1A (NICKEL)
1. ALL DIM ARE IN INCHES



RECOMMENDED
PANEL CUTOUT
SCALE: 2/1

REVISIONS			1-0010	SH 1C
REV	EO	DESCRIPTION	DWN	APPROVED
D	13257	SH 2; ±.030 TOLERANCE REPLACES ±.003 ON .757 DIMENSION; SEE ECD	DKC	2/18/00

QTY	DESCRIPTION				PART NUMBER		ITEM
TOL UNLESS SPECIFIED		TROMPETER ELECTRONICS, INC.			BJ21 / UBJ21		
.XX ±							
.XXX ± .005							
.XXXX ±							
ANGLES							
DWN	DKC	2-3-00	MATERIAL	CODE IDENT	DRAWING NO.		REV
CHK	<i>h</i>	2-18-00	_____	14949	1-0010		D
ENGR	<i>h</i>						
APPR	<i>h</i>	2-18-00	SCALE 4/1	DATE 5-12-82	SHEET		1C