

Representative Image

Catalog No. 54806

Description: 2WAY CU SPLICE CONN LNGBRL NO4 BRN

UPC No 786210548067

Home > Connectivity & Grounding > Color Keyed / Blackburn > Wire or cable compression splice

Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size #4 AWG, Length 1.75 Inches, Diameter 0.39 Inches, Tin Plated, Die Code 29, Die Color Code Gray

Descriptors

Category	Wire or cable compression splice
Special Features	Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.
Application	Applications certified to 600 V and recommended up to 35 kV¥

Specifications

Material	Copper
Finish	Tin-Plated
Color	Gray
Voltage Rating	600 V

Classifications

Brand Name	Color Keyed / Blackburn
Standard	UL E9809

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC001059 Crimp splices for copper conductor
Material	Copper
Surface protection	Tinned

Downloaded from Arrow.com.

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	1097195_2015-02-20	N/A
UL	E9809	N/A	ZMVV	N/A	N/A

Downloaded from Arrow.com.