MATERIALS AND FINISHES:

SMA JACK STR CONNECTOR:

BODY, CRIMP TUBE, JAM NUT: BRASS PLATED GOLD

CENTER CONTACT: BERYLLIUM COPPER PLATED GOLD

INSULATOR: TEFLON

LOCK WASHER: PHOSPHOR BRONZE PLATED GOLD

GASKET: SILICONE RUBBER

CONNECTOR:

MHF® I LK

MATED HEIGHT: 2.90MM MAX


CABLE: 1.32MM CABLE BLACK


NOTES:


PACKAGING BY PLASTIC BAG

PERFORMANCE REQUIRMENTS:

1. FREQUENCY: DC~ 6GHz
2. IMPEDANCE: 50 OHMS
3. TEST 100% CONTINUITY
4. TEST 100% HI-POT: AC 350 V@0.5mA







RECOMMENDED MOUNTING HOLE

PART No.	IN	MM
	A	
73230-6205	2.000±.118	50.80±3.00
73230-6204	4.000±.197	101.60±5.00
73230-6203	6.000±.197	152.40±5.00
73230-6202	8.000±.197	203.20±5.00
73230-6201	10.000±.197	254.00±5.00
73230-6200	12.087±.236	307.00±6.00

DOCUMENT STATUS	P1	RELEASE DATE	2023/07/07 09:38:57

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FP = 0
DIVISIONAL SYMBOLS

DIMENSION UNITS: mm
SCALE: NTS
GENERAL TOLERANCES (UNLESS SPECIFIED)
ANGULAR TOL ± °
4 PLACES ±
3 PLACES ±
2 PLACES ±
1 PLACE ±
0 PLACES ±
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:
ADD NEW PART No: 732306201,732306202, 732306203,732306204, 732306205

EC NO: 755979
DRWN: JCHEN108 2023/07/07
CHK'D: MYLU07 2023/07/07
APPR: LCHEN03 2023/07/07

INITIAL REVISION:
DRWN: JCHEN108 2022/07/08
APPR: LCHEN03 2022/09/22

THIRD ANGLE PROJECTION
DRAWING: C-SIZE
SERIES: 73230

molex

CA, SMA JACK STR BKHD IP68 TO MHF® I LK WITH 1.32MM CABLE EWR#15294-D

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
732306200	PSD	000	B

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1

Downloaded from Arrow.com.