

Coaxial PCB Connector 82_MBX-50-0-29/11-_N

Description

Straight PCB jack

Interface Standards
HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.00116 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EC (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	PA (Polyamide)	
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing	DOU-00262050
Catalogue drawing	DCA-00262072
Mounting hole	DPA-00144881

Ordering Information

Tape and Reel package	82_MBX-50-0-29/11-_NM
Single package	82_MBX-50-0-29/11-_NE
Bulk 100 pcs package	82_MBX-50-0-29/11-_NH

Remarks

PCB connector with stand-offs