

Representative Image

Catalog No. F10711

Description: NON-INS - TUB RING TERM, 4, 1/4, ME

UPC No 786210829661

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Non-Insulated Tubular Ring Terminal, Length 1.37 Inches, Width .55 Inches, Bolt Hole 1/4 Inch, Wire Range 4/4AN, Copper, Tin Plated

Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indentor or double indentor (recommended for solid wire).

Specifications

Voltage Rating	600 V
Material	Copper
Color	Metallic

Classifications

Brand Name	Sta-Kon
Standard	UL E9809

Dimensions

Wire Size	4 AWG

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Slender flange model	N
Insulated	N
With sight-hole	Y

by ABB

Downloaded from Arrow.com.

ETIM	EC001051 Tube cable lug for copper conductors
Material	Copper
Surface protection	Tinned
Number of mounting holes	1

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.