ME 22,5 OT-MSTBO KMGY FL COM - Upper housing part

1116375

https://www.phoenixcontact.com/us/products/1116375

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Upper housing part for connectors with header, color: light gray (similar RAL 7035)

Commercial data

Item number	1116375
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	NULL
Product key	ACHAAD
GTIN	4063151042158
Weight per piece (including packing)	11.9 g
Weight per piece (excluding packing)	11.2 g
Customs tariff number	85389099
Country of origin	DE

Downloaded from Arrow.com.

Technical data

Product properties

Product type	Upper housing part
Housing type	DIN rail housing
Housing series	ME
Type	Upper housing part for connectors with header

Material specifications

Color (Housing)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
Housing material	PA

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

PCB data

Type of PCB mount	Latching

Mounting

Mounting type	Latching with lower housing part

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

Downloaded from Arrow.com.

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1116375

UL Recognized
Approval ID: E240868

Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

UNSPSC

UNSPSC 21.0	31261501

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com

Downloaded from Arrow.com.