



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide
--------------------	--

Physical

Depth	53.3 cm
Height	7.6 cm
Net weight	19.09 kg
Width	21.6 cm

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cartridge
Battery voltage	48 V

Battery type	Lead-acid battery
Number of battery replacement quantity	1

Packing Units

Package 1 Weight	20.45 kg
Package 1 Height	22.9 cm
Package 1 width	39.4 cm
Package 1 Length	76.8 cm
Number of Units in Package 3	12

Offer Sustainability

Sustainable offer status	Green Premium product
Energy Star	ENERGY STAR UPS V1.0 (USA) 
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	1 year repair or replace, 30 days (Japan only)
----------	--