



Part Number : [135240001](#)
Product Description : Button RFID Tag, 1.9m Read Range, 34.00mm Diameter Footprint, For Metal Surfaces, Screw or Rivet Attachment
Series Number : 13524
Status : Active
Product Category : Asset Tracking



Documents & Resources

Drawings
[135240001_sd.pdf](#)

Specifications
[135240001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Asset Tracking
Series	13524
Description	Button RFID Tag, 1.9m Read Range, 34.00mm Diameter Footprint, For Metal Surfaces, Screw or Rivet Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Metal Surfaces
UPC	196823154195

Electrical

Frequency	902-928 MHz
-----------	-------------

Physical

Mounting Style	Adhesive, Screws
Outer Diameter	34.00mm
Packaging Type	Bag
Read Range	2.0m
Thickness	6.00mm
Width	N/A