
This document was generated on 03/03/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0003092014
Status: Obsolete
Overview: standard_093
Description: 2.36mm (.093") Diameter Standard .093 Pin and Socket Plug Housing, 1 Circuit
Replacement Part Number: NONE



Series image - Reference only

Documents:
Drawing (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	1951
Application	Power
Comments	17.0A max. can be achieved when housing is used with 42477 or 42478 terminals
Obsolete Date	2001/01/01
Overview	standard_093
Product Name	Standard .093"
Replacement Part Number	NONE

Physical

Circuits (maximum)	1
Color - Resin	Natural
Flammability	94V-2
Gender	Dual
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	14A

Material Info

Old Part Number	1951-P

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
1951Series

Mates With
1951r

Use With
1189 Crimp Terminals, 1190 Crimp Terminals, 1380 Male Crimp Terminals, 1381 Female Crimp Terminals, 1433 Crimp Terminals, 1434 Male Crimp Terminals, 1973 , 2151 , 2273 , 2870 , 2871 , 4272 , 4550 , 6271 , 6310 , 42477 , 42478

This document was generated on 03/03/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.