



Part Number : [1300060847](#)
Product Description : Mini-Change A-Size Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 18 AWG, Yellow PVC Cable, 10.0m (32.81') Length
Series Number : 130006
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 104000A05M100



Documents & Resources

Drawings
[1300060847_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 18 AWG, Yellow PVC Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	78678834655

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	5.6A
Voltage - Maximum	300V

Physical

Cable Diameter	7.14mm (.281")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC

Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	711.232/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	AWM 2661
Wire Size (AWG)	18

This document was generated on Mar 18, 2025