

## Data Sheet | Item Number: 209-129

Operating tool; made of insulating material; 1-way; for 279 Series; natural

<https://www.wago.com/209-129>



Color: ■ natural

### Technical data

|                    |          |
|--------------------|----------|
| Number of spacings | 1 -times |
|--------------------|----------|

### Physical data

|              |                        |
|--------------|------------------------|
| Width        | 20.5 mm / 0.807 inches |
| Height       | 20.5 mm / 0.807 inches |
| Depth        | 141 mm / 5.551 inches  |
| Blade length | 70 mm                  |
| Grip length  | 71 mm                  |

### Mechanical data

|                      |                     |
|----------------------|---------------------|
| Tip type             | Operating 2,5 x 0,8 |
| Continuous blade     | No                  |
| Blade type           | Straight            |
| Roll-away protection | Yes                 |
| Hanging eyelet       | Yes                 |
| Grip marking         | Yes                 |

### Material data

|                                    |  |
|------------------------------------|--|
| Color                              | natural                                    |
| Material group                     | I  |
| Insulation material (main housing) | Glass fiber-reinforced polyamide (PA66 GF) |
| Flammability class per UL94        | HB   |
| Fire load                          | 0.283 MJ                                   |
| Weight                             | 9.4 g                                      |

**Commercial data**

|                       |                                |
|-----------------------|--------------------------------|
| Product Group         | 2 (Terminal Block Accessories) |
| PU (SPU)              | 100 (1) pcs                    |
| Packaging type        | Box                            |
| Country of origin     | DE                             |
| GTIN                  | 4017332096393                  |
| Customs tariff number | 39269097900                    |

**Product Classification**


|             |                      |
|-------------|----------------------|
| UNSPSC      | 27112809             |
| eCl@ss 10.0 | 27-14-11-92          |
| eCl@ss 9.0  | 27-14-11-92          |
| ETIM 9.0    | EC002848             |
| ETIM 10.0   | EC002848             |
| ECCN        | NO US CLASSIFICATION |

**Environmental Product Compliance**



|                        |                         |
|------------------------|-------------------------|
| RoHS Compliance Status | Compliant, No Exemption |
|------------------------|-------------------------|

**Downloads**

**Environmental Product Compliance**

|  |  |  |   |
|--|--|--|---|
| <b>Compliance Search</b>                 |  |  |   |
| Environmental Product Compliance 209-129 |  |  |  |

**Documentation**

|                 |            |                 |   |
|-----------------|------------|-----------------|---|
| <b>Bid Text</b> |            |                 |   |
| 209-129         | 19.02.2019 | xml<br>2.56 KB  |  |
| 209-129         | 11.09.2017 | doc<br>23.50 KB |  |

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](http://www.wago.com)