



Part Number : [1301350231](#)
Product Description : Super-Safeway Heavy-Duty Multiple Outlet Box, (4) NEMA 5-15 Single with Flip Lids, 7.62m (25.0') Cord Length, 12/3 SOOW Cord, NEMA 5-15 Plug
Series Number : 130135
Status : Obsolete
Product Category : Power Distribution
Engineering Number : 32W47A123



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Power Distribution
Series	130135
Description	Super-Safeway Heavy-Duty Multiple Outlet Box, (4) NEMA 5-15 Single with Flip Lids, 7.62m (25.0') Cord Length, 12/3 SOOW Cord, NEMA 5-15 Plug
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Name	Watertite
Type	Multiple Outlet Box
UPC	78678876181

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	125V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	7.62m (25.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes

Material - Housing	Rubber
Mounting Style	Portable
Number of Receptacles	4
Packaging Type	Carton
Receptacle Type	Single

This document was generated on Sep 13, 2025

Obsolete