



This Linksys® MFEFX1 compatible SFP transceiver provides 100Base-FX throughput up to 2km over multi-mode fiber (MMF) at a wavelength of 1310nm using a LC connector. It is guaranteed to be 100% compatible with the equivalent Linksys® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. It is built to meet or exceed the specifications of Linksys®, as well as to comply with MSA (Multi-Source Agreement) standards to ensure seamless network integration. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits

Supports data rates up to 100Mbps	SFP transceiver module
LC ports designed for use with Multimode Fiber	1310nm wavelength signaling
Supports up to 2 kilometers of cabling	

Specifications

General Info			
Product Line	C2G	Color	Silver
UPC Number	757120669807	Country Of Origin	United States
Application Sector	Commercial, Industrial	Type	Transceiver
Technical Information			
Fiber Optic Cable Type	Multimode	Max Distance Support	2 km
Connector 1	SFP Male		