




**Part Number :** [1062835003](#)

**Product Description :** Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8 LC Multimode 50/125µm 3.00mm Round Cable Plenum, Standard Bandwidth(OM2), 5.0m (16.40' ) Length

**Series Number :** 106283

**Status :** Active

**Product Category :** Fiber Optic Cable Assemblies



---

## Documents & Resources

### Drawings

[Drawing 1062835003\\_sd.pdf](#)

### Specifications

[Product Specification 885366203-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106283
Description	Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8 LC Multimode 50/125µm 3.00mm Round Cable Plenum, Standard Bandwidth(OM2), 5.0m (16.40' ) Length
Connector to Connector	MTP-to-LC
Mode	Multimode Enhanced
Product Family	zQSFP+ and QSFP+ Integrated Product Solutions
Product Name	MPO,QSFP Plus,QSFP+
UPC	822350976763

### Agency

CSA	LR64395
UL	E72548

### Physical

Boot Type	N/A
Cable Length	5.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Net Weight	82.234/g
Single Ended	No
Wire/Cable Type	Round

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

This document was generated on Sep 28, 2024