
Part Number : 900590009
Product Description : 2.54mm Pitch C-Grid Micro Shunt, Low Profile, 0.381µm Select Gold (Au) with Gold (Au) Flash Plating
Series Number : 90059
Status : Active
Product Category : Connector Accessories



Documents and Resources

Drawings

900590009_sd.pdf

PK-90059-001-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-90059-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	90059
Description	2.54mm Pitch C-Grid Micro Shunt, Low Profile, 0.381µm Select Gold (Au) with Gold (Au) Flash Plating
Component Type	Shunt
Product Name	C-Grid,C-Grid III,SL
UPC	800753539143

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	3.0A

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural

Downloaded from Arrow.com.

Flammability	94V-0
Gender	Female
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Material - Resin	Polyester
Net Weight	0.072/g
Number of Rows	1
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.203µm
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Surface Mount

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	(0.64)/.025 square and round pins

Downloaded from Arrow.com.