

**Part Number :** [191930017](#)

**Product Description :** VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Mylar Tape Carrier

**Series Number :** 19193

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Part Number :** AA-321-10T



---

## Documents and Resources

### Drawings

[191930017 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753038479

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.480/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.21mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm <sup>2</sup>	0.25-1.50

---

## Application Tooling

### Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270034</u>
Mini-Mac Applicator	<u>638853800</u>

---

This document was generated on Jun 08, 2026