

# SEK CAB FLAT STD AWG28/7 14P 100m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 014 7004
Specification	SEK CAB FLAT STD AWG28/7 14P 100m
HARTING eCatalogue	<a href="https://b2b.harting.com/09180147004">https://b2b.harting.com/09180147004</a>

## Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)

## Version

Cable length	100 m
Number of cores	14
Core structure	AWG 28/7

## Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved -20 ... +105 °C moved
Impedance	100 Ω
Insulation resistance @ 20 °C	≥20 MΩ x km

## Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	2,790 g
Net weight	21 g/m
Country of origin	Germany
European customs tariff number	85444991
GTIN	5713140024403
ETIM	EC003249
eCl@ss	27061801 Data and communication cable (copper)