Specifications



Photo is representative

Eaton C22-DL-R-K01-24-P62

Eaton, 22.5 mm RQM Compact Pushbutton,Red,Plastic Actuator,Silver bezel,1.0 m flying lead wire,1NC,IP65, IP67, IP69K,Illuminated,LED,24 Vac/Vdc Light Unit,Flush mounting,5,000,000 operations,Momentary,22.5 mm,Flush Pushbutton,C22 Series

General specifications

PRODUCT NAME	Eaton C22 compact pushbutton
CATALOG NUMBER	C22-DL-R-K01-24-P62
EAN	4015081810819
PRODUCT LENGTH/DEPTH	41.73 in
PRODUCT HEIGHT	1.18 in
PRODUCT WIDTH	1.18 in
PRODUCT WEIGHT	0.103256 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DIN VDE 0600
CERTIFICATIONS	EN 60947 IEC 60947 CSA Certified UL Listed
PRODUCT TYPE	Compact pushbutton

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Compact pushbutton
ACTUATOR COLOR	Red
BEZEL	Silver
ACTUATOR FUNCTION	Momentary
ENCLOSURE	IP69K IP65 IP67
ACTUATOR MATERIAL	Plastic
OPERATING MODE	Momentary
CONTACT CONFIGURATION	1 NC
ILLUMINATION	Illuminated
SERIES	C22
LIGHT UNIT TYPE	LED
LIGHT UNIT VOLTAGE	24 Vac/dc
OPERATING CYCLES	5 million
MOUNTING METHOD	Flush
DEGREE OF PROTECTION	NEMA 13 NEMA 4X
PRODUCT CATEGORY	Flush pushbutton
SIZE	22.5 mm

Resources

MULTIMEDIA	How to size and select a Power Supply
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C22-DL-R-K01-24-P62
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Powering Business Worldwide

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.