

## Internal SAS Cable, mini-SAS (SFF-8087) to 4-in-1 32pin (SFF-8484), 3-ft (0.91 m)

MODEL NUMBER: S510-003



### Highlights

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal Mini-SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths ( up to 6Gbps )
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution

### Package Includes

- 3ft Internal SAS Cable, Mini-SAS SFF-8087 to SFF-8484

### Features

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal iPass assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths ( up to 6Gbps )
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution
- For Controller to Backplane applications

## Specifications

OVERVIEW	
UPC Code	037332143365
Technology	SAS; Ribbon/Internal
CONNECTIONS	
Side A - Connector 1	SFF-8087
Side B - Connector 1	SFF-8484
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.