




FCIconnect.com


Copyright FCI



PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	GLASS FILLED THERMOPLASTIC RATED.(UL94V-0)	1	COLOR:BRACK
2	CONTACT	BRASS	n	PLATING CONTACT AREA:GOLD OVER NICKL TERMINAL AREA:TIN (LEAD FREE)
3	MOUNTING PLATE	BRASS	2	PLATING:TIN (LEAD FREE)

RECOMMENDED PC BOARD LAYOUT
(COMPONENT SIDE)

n:NO. OF CONTACTS
(10 TO 30 , ONLY EVEN POS.)



NOTE
1.Flatness for contact terminal and mounting plate must be within 0.1.
2.This product meets European Union Directives and other country regulations as described in GS-22-008.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family 590F			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title FLOATING BOARD TO BOARD RECEPTACLE CONNECTOR (GOLD PLATING AND LEAD FREE) (CAT.No.BTFW__R-3RBTALF)			
A	J07-0021	M.K	Jan.25,'07	angles	linear					
B	J08-0124	M.K	Mar.17,'08		± 0.3	scale	dwg no JSA 97226			
				dr	K.Higuchi	Mar.17,'08				
				engr	M.Koga	Mar.17,'08	type Product Customer Drawing			
				chr	K.Higuchi	Mar.17,'08				
				appd	M.Koga	Mar.17,'08	size A4			
sheet	revision									
index	sheet						Rev			