


PRODUCT NO.	DIM "A"	DIM "B"	PCB THICKNESS
62364-101	26.1	6.9	2.4 ~ 2.9mm
62364-102	26.7	7.5	3.0 ~ 3.5mm
62364-103	28.5	9.3	4.8 ~ 5.1mm



NOTE

- ① MATERIAL
 INNER CONTACT : BeCu (C1720)
 RETAINER : BeCu (C1720)
 INSULATOR : PTFE
 OTHERS : BRASS (C3602)

- ② PLATING
 INNER CONTACT : Au 0.8μm MIN.
 OTHERS : Au 0.3μm MIN.
 (UNDER : Ni 1.27μm MIN.)

mat'l. code					surface	tolerance	projection	product family	CODE
----					ISO 1302	ISO 406 ISO 1101	MM	METRAL	JP
ltr	description	ecn no	dr	date	angles	linear	scale	title	
A	RELEASED	J80421	Y.K	10/16/98		0.X ±0.3	MM	METRAL COAX COUPLER	
B	REVISED	J10388	Y.K	7/3/01		0.XX ±0.3		DIN-A-JJ (75Ω)	
C	REVISED	J10683	Y.K	11/8/01	0°±2°	0.XXX ±0.3	scale 5:1		
D	REVISED	J20160	Y.K	3/25/02	dr	Y.KODAIRA	10/18/98	dwg no	sheet 1 of 1 size
E	REVISED	J03-0309	Y.K	7/17/03	enrg	S.OKUDAIRA	3/5/07	62364	A4
F	REVISED	J07-0030	S.O	1/18/07	chr	R. Shoyu	3/16/07		
G	REVISED	J07-0147	S.O	3/5/07	appd	S. Shoyu	3/16/07	type	Customer Drawing
sheet	revision	G							Rev.
index	sheet	1							G