



Part Number : [734152262](#)
Product Description : 50 Ohms, MMCX Right-Angle Plug, Crimp, 1.13mm Cable, Plating Per Commercial Requirements, One Piece Per Bag
Series Number : 73415
Status : Active
Product Category : RF / Coaxial Connectors




Documents & Resources

Drawings
[734152262_sd.pdf](#)

3D Models and Design Files
[734152262_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73415
Description	50 Ohms, MMCX Right-Angle Plug, Crimp, 1.13mm Cable, Plating Per Commercial Requirements, One Piece Per Bag
Product Name	MMCX
Style	Cable
Type	Microminiature
UPC	884982653498

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	None
Net Weight	0.564/g
Orientation	Right Angle
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	1.13mm max.