


| ITEM NO. | PART NUMBER | DESCRIPTION                                                               | QTY. | COMPONENT NOTES |
|----------|-------------|---------------------------------------------------------------------------|------|-----------------|
| 1        | 30-01225    | Wire, 2C BC, 22 AWG, UL20280, 300V, 80C, 4.7 mm, braided shield, FT2, TPU | 1    |                 |



**Notes:**  
Total wire length for resistance calculation: 6500 mm

|           |            |                 |                                                                                                  |                                                                                           |                                                                                                                 |              |              |
|-----------|------------|-----------------|--------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|--------------|--------------|
| Revision: | Date:      | Description:    | Prepared:                                                                                        | Notes:                                                                                    | <div>TENSILITY</div> <div> tel 1.541.323.3228 800 877.670.7118<br/> fax 1.541.323.4202 web tensility.com </div> |              |              |
| A         | 10/17/2018 | Initial release | Verified:                                                                                        |                                                                                           |                                                                                                                 |              |              |
|           |            |                 | Dimensions are in millimeters.<br>Tolerances:<br>X: ± 0.5 mm<br>X.X: ± 0.3 mm<br>X.XX: ± 0.05 mm | Description:                                                                              | Size:                                                                                                           | Part number: |              |
|           |            |                 |                                                                                                  |                                                                                           | A                                                                                                               | 31-00007     |              |
|           |            |                 |                                                                                                  | Coiled cable, 2230 mm, 2C blunt cut to same, 22 AWG, 4.7 mm, TPU, shielded, 30-01225 wire | Scale: 1:1                                                                                                      |              | Sheet 1 of 1 |