
Part Number : 190710149
Product Description : InsulKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Length 36.25mm, Mylar Tape Carrier
Series Number : 19071
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : D-651-14XT



Documents and Resources

Drawings

190710149_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-009-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19071
Description	InsulKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Length 36.25mm, Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753071193

Agency

UL	E32244

Electrical

Voltage - Maximum	300V

Physical

Downloaded from Arrow.com.

Barrel Type	Closed - Brazed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	4.222/g
Packaging Type	Adhesive Tape on Reel
Stud Size	1/4" (M6)
Wire Insulation Diameter	9.78mm
Wire Size (AWG)	8
Wire Size mm^2	8.36

Application Tooling

This document was generated on Apr 23, 2026

Downloaded from Arrow.com.