

Power Matters.™

[Home](#) ▶ [60HQ100 \(#56362\)](#)

Products

- ▶ [Product Directory](#)
- ▶ [Applications](#)
- ▶ [Parametric Search](#)

60HQ100 (#56362)

Product Status

■ In Production

Related Links

[Technical support](#)
[How to Buy](#)
[Available Stock](#)
[Sales Contacts](#)
[RFQ/Samples](#)

Overview

Diagrams

Description

60Amp,90V-100V Schottky Rectifier in DO5 package.

Electrical Rating	Symbol	Min	Typ	Max	Unit
Forward Voltage (V)	V_F			0.89	V
Junction Capacitance (pF)	C_J		1250.00		pF
Reverse Current (uA)	I_R			1000.00	μA

Maximum Electrical Rating	Symbol	Min	Typ	Max	Unit
Forward Surge Peak Current (A)	I_{FSM}			1000.00	A
Output Current (A)	I_O			60.00	A
Reverse Voltage	V_R			100.00	V

This part can be found in the following product categories:

▶ [Power Discretes & Modules](#) ▶ [Diodes](#) ▶ [Si Schottky Rectifier Diodes](#)