



Specifications

Description AJT62A

2 pair

Technical Data AJT62A

Housing: PC + 30% glass-fiber UL94V-0
 Contact: 0.80mm thickness alloy C5210, tin plating over nickel

For use with 24 AWG Stranded Wire and/or 26 AWG Solid Wire

Ordering Information

AJT62A	4	4	1	5	-	1
Type	Positions	Contacts	Ports	Plating w/o Tin Over color	Nickel	coding

METZ CONNECT	P/N: AJT62A4415-1
------------------------	-------------------

Desc.: 110 IDC connector

Date: 5-14-07 Drawn By: Donna Mears
 Dimensions in mm Verified By: Mike Balekjian

Tolerance
unless otherwise specified
.X ± 0.38
.XX ± 0.25
.XXX ± 0.10