Part Number : 330014005
Product Description : MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm^2, Right Reel Payoff
Series Number : 33001
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

330014005_sd.pdf

313025040-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-33012-002-001.pdf

AS-33012-002-CH-001.pdf

AS-33012-002-FR-001.pdf

PS-33012-002-001.pdf

TS-33001-003-001.pdf

TS-33001-004-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44; 34
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-

Downloaded from Arrow.com.

	DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	33001
Description	MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm^2, Right Reel Payoff
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Comments	For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers.
Product Name	MX150
UPC	884982250857

Electrical

Downloaded from Arrow.com.

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Physical

Gender	Female
Grip Code	M3
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	0.443/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.70mm max.
Wire Size (AWG)	N/A
Wire Size mm^2	0.35-0.50

Mates With / Use With

Use with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Female Connector Assemblies	33472
MX150 Mat-Sealed Single Row Female Connector Assemblies	33471

Application Tooling

Global

Description	Part Number
Extraction Toolkit for MX150 Connectors	2002220700
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid,	638131500

Downloaded from Arrow.com.

SPOX, and Wire-to-Motor Terminals	
Hand Crimp Tool for ISO (M3) Receptacle Terminals	638233700

Downloaded from Arrow.com.