

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 10724816

☐ Compare

60070151 - DCS-1 9.5 Series Female Sealed Tin Plating Terminal, Cable Range 2.50 - 4.00 mm2

☐ Compare

DCS-1 9.5 Series Female Sealed Tin Plating Terminal, Cable Range 2.50 - 4.00 mm2

Part # 60070151



[Question about this product?](#)

Attributes

Documents (1)

Part # :	60070151
Description :	DCS-1 9.5 Series Female Sealed Tin Plating Terminal, Cable Range 2.50 - 4.00 mm2
Product Type :	Terminal
Status :	✓ Active
Blade size [mm] :	9.5
Series :	9.5
Gender :	Female
Sealable :	Sealed
Material :	CuCrSiTi/CrNi
Weight [g] :	4
Plating :	Tin
Maximum Cable Diameter [mm] :	3.70
Minimum Cable Core Cross Section [mm2] :	2.50
Maximum Cable Core Cross Section [mm2] :	4.00
Remarks :	Former FCI Product, Delphi PN:10724816,DCS-1, Auxiliary steel spring in CrNi, High current carrying capacity, Protected contact springs, Silver plated versions available, Pitch: 12 mm unsealed / 12.5 mm with SWS

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.