





PIN OUT:



P/N	L
105-1030-BL-00050-1	500±20
105-1030-BL-00100-1	1000±30
105-1030-BL-00200-1	2000±50
105-1030-BL-00300-1	3000±50
105-1030-BL-00500-1	5000±50

ITEM	DESCRIPTION	SPECIFICATION	Q'TY
1	Conn.	Type C Contact Gold Plated 3u",Insulator Black, OTG Rd=5.1kΩ,C1=10nf +Cable Clamp+Shell	1
2	Conn.	USB3.0 B/M Contact G/F,Insulator Blue+Cable Clamp+Shell	1
3	Outer molding	45P PVC Color:Black	A/R
4	Cable	7/0.12TS+PEF,ID:0.90*2C+D7/0.12TS+AL+M)*2P+(7/0.12TS+HDPE,ID0.7*1P)+ (7/0.2TS+PVC ID:1.05*2C)+(PP 3800X2)+AL+D7/0.12BS+96/0.12ALMAG+PVC OD:5.5mm Black	A/R

F				DRAWN:	GENERAL TOLERANCE: .X=±0.3 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology	
E							
D							
C				CHECKED:	UNIT: MM	DESCRIPTION: TYPE C M TO USB3.0 B M CABLE	SIZE A4
B					SCALE:1:1		
A	25–Aug–2022		Andrew	APPROVAL:	SHEET: 1/1	PART NO: 105-1030-BL-00XXX-1	
REV	DATE	FILE	BY		PROJECTION: 		