Part Number : 1202480007
Product Description : M12 Signal, A-Coded, MPIS Passive Distribution Box, Top-Mount, 4 Poles, 4 Ports, NPN LED Indicators, WSOR Home Run Cable, 5.0m (16.4') Length
Series Number : 120248
Status : Active
Product Category : Passive Distribution Boxes
Engineering Part Number : BTB400N-FBW-05



Documents and Resources

Drawings

1202480007_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	120248
Description	M12 Signal, A-Coded, MPIS Passive Distribution Box, Top-Mount, 4 Poles, 4 Ports, NPN LED Indicators, WSOR Home Run Cable, 5.0m (16.4') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12),MPIS
UPC	889056329590

Agency

UL	E152210

Electrical

Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	NPN
Voltage - Maximum	10-30V DC
Wiring Configuration	Single I/O per Port

Physical

Bus I/O	N/A

Downloaded from Arrow.com.

Cable Connector Orientation	Straight
Home Run Cable Length	5.0m
Home Run Connector	N/A
Home Run Interface	Pigtail
Keyway	A-Coded
LED Indicator	NPN Sensors
Material - Cable Jacket	TPU
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	628.300/g
Orientation	Top-Mount
Poles	5
Poles (wired)	4
Ports	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	TPU (WSOR)

Downloaded from Arrow.com.