


CATALOG LISTING
1TL887 SERIES CHART 2
PAGE 1 OF 1
ISSUE 5
RELEASE NO PR-14057-T
CHECK
11MAY05
AK
JAF 28 JUN 94
RASTER
DRAWN

MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED MFG CODE 91929

SWITCH-TOGGLE

CATALOG LISTING
1TL887 SERIES
CHART 2


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH



SCALE FULL
DO NOT SCALE PRINT
UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE
ONE PLACE .01
TWO PLACE .001
THREE PLACE .0001
ANGLES .005
WEIGHT .08 LBS APPROX

L 191		L 192	
15A	125, 250, 277 VAC	10A	125, 250, 277 VAC
1/2 HP	125 VAC	1/4 HP	125 VAC
1 HP	250, 277 VAC	1/2 HP	250, 277 VAC
5A	125 VAC "L"	3A	125 VAC "L"
UL CE		UL CE	

CATALOG LISTING △ 6	AVAILABLE LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERING DETAILS	CIRCUIT MADE WITH TOGGLE LEVER IN △ 7			CURRENT CAPACITY (AMPS)								
		KEYWAY SIDE (1-2)	CENTER (1-2)	OPPOSITE KEYWAY (2-3)	RESISTIVE LOAD DC VOLTS			LAMP LOAD AC VOLTS		IND. LOAD			
					28	125	250	28	125	28	125		
ITL887 - 1	AB,D,E,F,G,H,J,K,L,M,N,P	ON	OFF	ON	20	.75	.5	15	6	5	3	15	10
ITL887 - 2	D, F, G	OFF	NONE	ON									
ITL887 - 3	D, F, G	ON	NONE	ON									
ITL887 - 2I	E, F, K, M	NONE	OFF	ON									
ITL887 - 3I	E, F, K, M	NONE	ON	ON									
(REFER TO L191 FOR UL LISTING)													
ITL887 - 4	F	MOM OFF	NONE	ON	15	.75	5	15	6	4	2	10	7
ITL887 - 5	E, F, K, L, M, N	MOM ON	OFF	ON									
ITL887 - 6	F	MOM ON	NONE	OFF									
ITL887 - 7	E, L, N	MOM ON	OFF	MOM ON									
ITL887 - 8	F	MOM ON	NONE	ON									
(REFER TO L192 FOR UL LISTING)													
ITL887 - 5I	E	NONE	ON	MOM ON									
ITL887 - 6I	E	MOM ON	OFF	NONE									



- NOTES
- SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 - FURNISHED UNASSEMBLED
 - FOR TERMINAL COVER SEE MICRO SWITCH CAT. LIST. 5PA7
 - KEYWAY SHOWN ON LEFT SIDE
 - SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE OF TOGGLE LOCKING. SEE CHART FOR AVAILABLE LOCKING COMBINATIONS
 - APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
 - FROM BOTTOM OF KEYWAY TO MAJOR DIA. OF 15/32 THREAD
 - CONFORMS TO REQUIREMENTS OF MIL-DTL-3950 EXCEPT: GOLD PLATED CONTACTS
 - INSERT HAS A .15 WIDE CLEANING SLOT AT EACH END INLINE WITH TOGGLE TRAVEL

