







PC board drilling dimensions
(after plating - thickness: 1.60 to 3.20 mm)



TIN LEAD PART NUMBER

PART NUMBER	
flash gold	D50S91C4PL00
0.76µ gold	D50S91C6PL00

LEAD FREE PART NUMBER

PART NUMBER	
flash gold	D50S91C4PL00LF
0.76µ gold	D50S91C6PL00LF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

European Views

rev	ecn no	dr	date
A	-	JOU	1996/08/12
B	LS05-004	MPE	2005/02/11
D	-	MPE	2005/11/28
E	LS06-0097	LGO	2006/07/29
F	LS06-0140	LGO	2006/09/25
-	-	-	-
-	-	-	-

www.fciconnect.com			surface 150 1302 ✓		tolerance std 150 406 150 1101		projection 		mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	JOUBERT	1996/08/12	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	1996/08/12			0.XX	±0.1				
Chr	LEGARE	1996/08/12			0.XXX	±0.1				
Appr	LEGARE	1996/08/12	Product family				D-SUB	ECN LS06-0097 Spec ref -		
			title FEMALE CONNECTOR DELTA D STRAIGHT PRESS-FIT.				dwg no C01-8646-0272		Rev. F	
catalog no			-				CUSTOMER		sheet 1 of 1	



FEMALE CONNECTOR DELTA D
STRAIGHT PRESS-FIT.

C01-8646-0272
CUSTOMER sheet 1 of 1