

Product Search

Product Catalog

[Products](#)[Lamps & LED-Lamps](#)[Neon lamps](#)[Wired Terminal](#)

Markets

[Automotive](#)[Aviation](#)[Gaming](#)[Illumination](#)[Transport](#)[Custom Projects](#)

POS-CCE - Romania Sibiu

Product details

Article: 08110118





Description

Designation: Neonlamp, wire terminal, 1mA, red

Optical features

Colour: red

Electrical features

Current: 1 mA
Max. Striking Voltage AC: 95 V
Max. Striking Voltage DC: 135 V
Series resitors at 230V: 150 kOhm (W)
Series resitors at 110V: 47 kOhm (W)

Mechanical features

Socket: wire terminal
Diameter: 6 mm

Gallery





Click on a small picture to select it. Click the large image to view full size.



Multivoltage LED Lamps

Covering the voltage range of 6 to 32V
Available in all colours and BA9s socket



Stock inquiry

Latest News

2014-08-28
New CML catalogue: "CML LED lamps for signalisation and LED panel mount indicators"
>> [More details](#)

2014-07-07
Optimized BA15d LED lamp for use in light towers
>> [More details](#)

2013-11-10
StockCheck function added to the website
>> [More details](#)