




Part Number : [2257753012](#)
Product Description : HFM Straight Quad Jack-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Key Z Water Blue, RG-174 Cable, 1000.00mm Length, 50 Ohms
Series Number : 225775
Status : Active
Product Category : RF Cable Assemblies



Documents and Resources

Drawings

[2257753012 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[2079110012-000.pdf](#)
[2088700000PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF Cable Assemblies
Series	225775
Description	HFM Straight Quad Jack-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Key Z Water Blue, RG-174 Cable, 1000.00mm Length, 50 Ohms
Application	Automotive, RF, Wire-to-Wire, Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	HFM-to-Pigtail
Product Name	High-Speed FAKRA Mini (HFM)
Type	RF Cable Assembly
UPC	198930365631

Electrical

Impedance	50Ω
-----------	-----

Physical

Cable Length	1000.00mm
Gender	Jack
Material - Metal	Spring Bronze
Material - Plating Mating	Gold
Material - Resin	Polybutylene Terephthalate (PBT)

Net Weight	54.054/g
Packaging Type	Carton
Single Ended	Yes
Wire/Cable Type	RG-174

Mates With / Use With

Mates with Part(s)

Description	Part Number
High-Speed FAKRA Mini (HFM) Right-Angle, Through Hole Quad Headers	<u>208244</u>

This document was generated on May 13, 2026