

Johanson Part Number 2450LP14B0100001T

Johanson Part Number: 2450LP14B0100001T	Johanson Company: JTI
Legacy P/N: 2450LP14B100T	Size for Capacitors (EIA): None
Description: Low Pass Filters, 0603, 2400-2500MHz, 3W, 0.5dB, 2.45GHz Harmonic Low Pass Filter, SMD, Ni/Sn (RoHS), 7" Reel Paper Tape	Specification Number: None
Life Cycle Stage: Active	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.028
Schedule B: 8534.00.00.85	Thickness (Min): 0.020
ITAR: No	End Band(Min): 0.00
ECCN: EAR99	End Band (max): 0.012
RoHS Compliance: Yes, RoHS 10/10	Standard Item: No
REACH: Yes	Lead Time Typical (Weeks)*: 16
Country of Origin: TW	Length (Min): 0.059
Product Family: Integrated Passive Components	Length (Max): 0.067
Product Subfamily: Low Pass Filters	Width (Min):0.027
Capacitance Value: None	Width (Max): 0.035
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Paper Tape
Dielectric Temp Coefficient: None	Packaging Qty: 4000
Termination: 0	Operating Temp Range: -40°C to +85°C
Marking: Special	Storage Temp Range (Packaged): +5°C to +40°C with RH 20% to 70%
Product Release Date: Jan. 6, 2006	Storage Temp Range (None Operating): -65°C to +125°C
Harmonization: 8534.00.00.85	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://johansontechnology.com/low-pass-filters>

Printed from: <https://www.johansontechnology.com/part/2450LP14B0100001T/>