



Part Number : [734152161](#)
Product Description : MMCX Plug, Right-Angle,
Solder, RG-405 (.086" Semi-Rigid) Cable, Brass Body,
Gold Flash (Au) Plating, Bulk, 50 Ohms
Series Number : 73414
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[734152161 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73414
Description	MMCX Plug, Right-Angle, Solder, RG-405 (.086" Semi-Rigid) Cable, Brass Body, Gold Flash (Au) Plating, Bulk, 50 Ohms
Application	RF
Product Name	MMCX
Style	Cable
Type	Microminiature
UPC	822348065394

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Physical

Cable Attachment	Solder
Gender	Plug
Keying to Mating Part	N/A
Net Weight	0.500/g
Orientation	Right Angle
Packaging Type	Bag

Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-405, .086" Semi-Rigid Coaxial

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Sep 17, 2025