

Cat5e/6 Shielded Surface-Mount Junction Box, 110 IDC, TAA

MODEL NUMBER: **N237-001-SH**



Fast, easy, cost-effective way to directly connect 2 Cat5e/6 cables without using couplers or connectors. Ideal for audio/video, voice and Ethernet applications.

Description

The N237-001-SH Cat5e/6 Shielded Surface-Mount Junction Box is a fast, easy, cost-effective method of directly connecting two Cat5e/6 cables without using couplers or connectors. Designed for completing audio/video, voice and Ethernet applications, this junction box comes with screws and double-sided adhesive tape for quick mounting, as well as cable ties for keeping the cables neat and secure. It's made from ABS UL 94V-0 plastic and is recommended for use with solid conductor cable. The UL-listed box is color-coded for 568A/B wiring for easy 110 punchdown termination. The shielded N237-001-SH protects the signal against EMI/RFI line noise and has a dedicated space on the punchdown block for grounding.

Features

Completes A/V, Voice and Ethernet Applications

- Directly connects 2 Cat5e/6 cables without couplers or connectors
- Uses standard 110 punchdown termination
- Recommended for use with solid conductor cable
- Protects against EMI/RFI line noise
- Dedicated space on punchdown block for grounding
- Color-coded for 568A/B wiring
- Mounting hardware and cable ties included
- Durable ABS UL 94V-0 plastic housing

TAA-Compliant

- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332197320

Highlights

- Uses standard 110 punchdown termination
- Recommended for use with solid conductor cable
- Color-coded for 568A/B wiring
- Protects against EMI/RFI line noise
- Dedicated space on punchdown block for grounding

Package Includes

- N237-001-SH Cat5e/6 Shielded Surface-Mount Junction Box
- Mounting hardware
- (2) Nylon cable ties



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	Cat5/5e; Cat6
Country/Region	Global
CONNECTIONS	
Side A - Connector 1	110 IDC
Side B - Connector 1	110 IDC
PHYSICAL	
Color	Silver
Total Number of Ports	0
Shipping Dimensions (hwd / in.)	0.25 x 4.90 x 4.09
Shipping Dimensions (hwd / cm)	0.64 x 12.45 x 10.39
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.