
LOC	DIST
J	

REVISIONS
変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECR-20-100815	01DEC2020	BDA	SW
	E1	REVISED PER ECR-21-102346	29APR2021	JP	VS



NOTES;

1. APPLICABLE HOUSING : CAP AND PLUG.
2. PRODUCT SPECIFICATION 108-5138
3. APPLICATION SPECIFICATION 114-5050
4. INSTRUCTION SHEET IS-105J
5. SELECTIVE GOLD PLATED AREA "C"
   0.0004mm MIN THICK OVER Ni PLATE
   ON INSIDE SURFACE
6. DOUBLE CRIMPING INSURATION DIA
   3.4mm MAX.

	錫めっき付・燐青銅 (PRE-TIN - PHOZ BRO)	-4	-4
	金めっき・黄銅 (GOLD PLATE - BRASS) 5	-3	-3
170359, 170360 170363, 170364	錫めっき付・黄銅 (PRE-TIN - BRASS)	170362-1	170366-1
嵌合相手型番 (MATING P/N)	材料・仕上 (MATERIAL - FINISH)	連鎖状端子型番 (STRIP P/N)	型番 (P/N)

WIRE RANGE 抱合電線断面積: 0.30~0.89mm² (AWG #22~#18)
INSULATION DIA 被覆外径 6: 1.5~2.4mm

DIMENSIONS; 単位 mm
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.4, ±1°0′

DWN T. Yamamoto 11 JAN 96
CHK M. Shiraishi 15 JAN 96
APVD M. Shiraishi 15 JAN 96

MATERIAL 材料 表参照 (SEE TABLE) 0.2t
FINISH 仕上 表参照 (SEE TABLE)

PRODUCT SPEC 製品規格 注記参照 (SEE NOTES) 2
APPLICATION SPEC 取付適用規格 注記参照 (SEE NOTES) 3
WEIGHT

TE Connectivity

NAME 名称
ミニ ユニバーサル メイテン ロック ソケット コンタクト ばら状端子
MINI UNIVERSAL MATE-N-LOK SOCKET CONTACT LOOSE PIECE

SIZE	CAGE CODE	DRAWING NO 番号
A4	00779	C-170366

CUSTOMER DRAWING

SCALE 尺度	SHEET	OF	REV
	1	1	E1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT ALL RIGHTS RESERVED.

Downloaded from Arrow.com.

参考図面